


C851



- **A** Low voltage cabling
■ 3x0,50 mm² cable
■ 2x0,50 mm² cable

- **B** Power cabling (230V)
■ 2x1,5 mm² +T cable
■ 2x1,5 mm² cable

EXAMPLE OF A TYPICAL INSTALLATION

| Ref | Q.ty | Description |
|-----|------|---|
| 1 | 1 | C851 gearmotor |
| 1 | 1 | C850 - C851 foundation plate |
| 1 | 1 | Galvanised rack 30x12 mod. 4 including weld-on fittings (4 pcs pack, 1 m each) |
| 1 | 1 | Plug in receiver 1 channel RP 433 SLH |
| 2 | 1 | FAACLIGHT 230V flashing light |
| 3 | 1 | Key operated button T10 E |
| 4 | 2 | Pair of photocells XP 30 |
| 4 | 2 | Column adapter |
| 4 | 2 | Low aluminium column 2 pc. pack) |
| 4 | 2 | Foundation plate for aluminium column (T10 - T11 - T10 E - T11 E) (10 pc. pack) |
| 1 | | XT2 433 SLH LR 2-channel transmitter |

ATTENTION: The configuration does not include safety devices (e.g.: active or passive safety ribs) which are determined according to the specific "risk assessment" of each installation (Ref.: UNI-EN European Standards 12445 and 12453). The indicated price does not include the installation costs and the expenses for masonry, electrical and metalwork preparations.